

## Product Specifications

PE2\* | Revised January 2016



5mm Close Mesh



3mm Extra Close Mesh

**Product Description:** Beards nets are an essential part of HACCP and ensure product safety. Manufactured from Polypropylene for excellent moisture transportation (wicking properties), the 3mm and 5mm mesh traps the hair at the root and allows the wearer to breathe easily without condensation build up.

Our Beard Snoods are made from a warp knitted polypropylene mesh and feature two metal detectable closures. Available in close mesh (5mm), or extra close mesh (3mm).

**Product Code:** PE2\*

**Batch Quantity:** Packs of 36 (on a card)

**Batch Weight:** 0.05kg

**Product Dimensions:** Adjustable

**Colour Availability:** Blue\* | Red | Green | White

**Product Advantages:**

- ✓ Detectable by conventional metal detection systems
- ✓ Highly visible colour range for easy visual identification
- ✓ Significantly reduces foreign body facial hair contamination
- ✓ Two integral metal detectable closures reduces the risk of the product itself becoming a foreign body contaminant

**Product Material(s):** Manufactured from Polypropylene covered elastic – to avoid skin allergy and discomfort.



## Product Variants:

| <u>Product Code</u> | <u>Colour</u> | <u>Mesh Size</u>     |
|---------------------|---------------|----------------------|
| PE2876TB            | Blue          | 5mm Close Mesh       |
| PE2876TG            | Green         | 5mm Close Mesh       |
| PE2876TR            | Red           | 5mm Close Mesh       |
| PE2876TW            | White         | 5mm Close Mesh       |
| *PE2926TB           | Blue          | 3mm Extra Close Mesh |

## Metal Detectability

These beard nets contain two 5mm metal closures which can be detected by correctly calibrated metal detection systems.

The detectability of this product will vary based upon the metal detection systems being used and their calibration. Detectability performance will vary based on, but not limited to the following factors:

- Detector Calibration Levels
- Food Product Type (E.g. Wet, Dry, Frozen, Liquid)
- Aperture Dimensions
- Contaminant Orientation

For this reason BST recommend that all our products be thoroughly tested on your metal detection systems by a trained and certified professional. It may be the case that your equipment needs to be recalibrated in order to reliably detect this product and its fragments. Such a professional should be available by contacting the manufacturer of your metal detection system.

---

## DISCLAIMER

The information provided in this product specification sheet is based on our experience and knowledge to date and we believe it to be true and reliable. This information is intended as a guide for your use of our products, the use of which is entirely at your own discretion and risk. We, BS Teasdale & Son Ltd, cannot guarantee favourable results and assume no liability in connection with the use of our products.

© 2014 BS Teasdale & Son Ltd. All Content, Data & Images are owned by BS Teasdale & Son Ltd and are protected by international copyright law.

